

Product User Guide

HiTemp140-FR



HiTemp140-FR

High Temperature Data Logger with a 2 inch Fast Response Probe



To view the full MadgeTech product line,
visit our website at madgetech.com.

Table of Contents

HiTemp140-FR Data Logger

Product Overview	2
Installation Guide	3
Device Operation	3
Product Maintenance	4
RMA Instructions	4
HiTemp140-FR General Specifications.....	5

Disclaimer & Terms of Use .. Back Cover

Product Overview

MadgeTech has designed the HiTemp140-FR, a high temperature data logger with an ultra-fast response time, to record temperature during rapidly changing thermal processes. This high temperature data logger features a 2 inch x 0.0625 inch diameter probe and is capable of recording up to 4 Hz, which is 4 times faster than other data loggers in this class. This allows the temperature sensor to quickly adapt and accurately record temperature variations in changing environments. Applications include oven profiling, steam sterilization, chamber mapping, seafood processing, flash freezing and more.

MadgeTech's entire HiTemp140 data logger series is designed with food grade stainless steel. The device can be placed in environments up to 140 °C and the probe is capable of measuring from -200 °C to +260 °C (-328 °F to +500 °F). The HiTemp140-FR is also available with an optional thermal shield enclosure to extend the operating range of the data logger to -200 °C to +250 °C (-328 °F to +482 °F).

The Trigger Settings feature of the HiTemp140-FR allows users to configure high and low temperature thresholds that when met or exceeded, will automatically start or stop recording data to memory. This data logger is capable of storing up to 65,536 date and time stamped readings and features a nonvolatile solid state memory which retains data even if the battery becomes discharged.

Submergibility

The HiTemp140-FR is rated IP68 and is fully submersible. It can be placed in environments up to 230 ft (70 m) of water.

O-Rings

O-ring maintenance is a key factor when properly caring for the HiTemp140-FR. The O-rings ensure a tight seal and prevent liquid from entering the inside of the device. Please refer to the application note "O-Rings 101: Protecting Your Data", found on the MadgeTech website, for information on how to prevent O-ring failure.

Trigger Settings

The device can be programmed to only record based off user configured trigger settings.

1. In the **Connected devices** panel, select the intended device to change the settings.
2. On the **Device** tab, in the **Information** group, click **Properties**. Users can also right-click on the device and select **Properties** in the context menu.
3. Click **Trigger** and configure the Trigger settings. Trigger formats are available in Window and Two Point (bi-level) mode. Window mode allows for one range of temperature monitoring and two point mode allows for two ranges.

Note: This product is rated for use up to 140 °C. Please heed the battery warning. The product will explode if exposed to temperatures above 140 °C.

Installation Guide

Installing the Interface cable

- IFC400 or IFC406

Refer to the “**Quick Start Guide**” included in the package.

Installing the software

Insert the Software USB stick in an open USB port. If the autorun does not appear, locate the drive on the computer and double click on **Autorun.exe**. Follow the instructions provided in the Wizard.

Device Operation

Connecting and Starting the data logger

- Once the software is installed and running, plug the interface cable into the docking station.
- Connect the USB end of the interface cable into an open USB port on the computer.
- The device will appear in the Connected Devices list, highlight the desired data logger.
- For most applications, select “**Custom Start**” from the menu bar and choose the desired start method, reading rate and other parameters appropriate for the data logging application and click “**Start**”. (“**Quick Start**” applies the most recent custom start options, “**Batch Start**” is used for managing multiple loggers at once, “**Real Time Start**” stores the dataset as it records while connected to the logger.)
- The status of the device will change to “**Running**”, “**Waiting to Start**” or “**Waiting to Manual Start**”, depending upon your start method.
- Disconnect the data logger from the interface cable and place it in the environment to measure. *Note: The device will stop recording data when the end of memory is reached or the device is stopped. At this point the device cannot be restarted until it has been re-armed by the computer.*

Note: Please refer to the Disclaimer & Terms of Use section on the back page of this guide for product usage recommendations.

Downloading data from a data logger

- Place the logger into the docking station.
- Highlight the data logger in the **Connected Devices** list. Click “**Stop**” on the menu bar.
- Once the data logger is stopped, with the logger highlighted, click “**Download**”. You will be prompted to name your report.
- Downloading will offload and save all the recorded data to the PC.

Product Maintenance

Battery Replacement

When replacing the battery, it is important to insert the battery with positive polarity pointing upward towards the probe. Failure to do so could result in product inoperability or potential explosion if exposed to high temperatures.



Recalibration

Recalibration is recommended annually. To send devices back for calibration, visit madgetech.com.

Call for custom calibration options to accommodate specific application needs.

Prices and specifications subject to change. See MadgeTech's terms and conditions at madgetech.com.

To send devices to MadgeTech for calibration, service or repair, please use the MadgeTech RMA Process by visiting madgetech.com.

HiTemp140-FR General Specifications

Temperature Sensor	100 Ω Platinum RTD	
Probe Measurement Range	-200 °C to +260 °C (-328 °F to +500 °F)	
Temperature Resolution	0.01 °C (0.02 °F)	
Calibrated Accuracy	±0.1 °C/±0.18 °F (20 °C to +140 °C/68 °F to +284 °F)	
Data Logger Response Time	In Air	In Water
	(hours : minutes : seconds : fractions of a second)	
	t ₆₀ - 00:00:39:00 t ₉₀ - 00:02:43:00	t ₆₀ - 00:00:10:00 t ₉₀ - 00:00:12:00
Reading Rate	4 readings per second up to 1 reading every 24 hours	
Memory	65,536 readings	
Start Modes	<ul style="list-style-type: none"> • Software programmable immediate start • Delay start up to 18 months in advance 	
Stop Modes	Manual or Timed (specific date and time)	
Trigger Settings	High & Low limits may be set. Once data meets or exceed sets limits, the device will record to memory. Bi-level start and stop triggers can also be programmed. Users can specify the number of readings to take after the device triggers.	
Readings in Trigger Settings Mode	10,922 readings	
Real Time Recording	May be used with PC to monitor and record data in real time	
Password Protection	An optional password may be programmed into the device to restrict access to configuration options. Data may be read out without the password.	
Memory Wrap Around	Yes	
Battery Type	3.6V high temperature lithium battery included; user-replaceable	
Battery Life	2 years typical (1 minute reading rate)	
Calibration	Digital calibration through software	
Calibration Date	Automatically recorded within device	
Data Format	Date and time stamped °C, °F, °R, K	
Time Accuracy	<ul style="list-style-type: none"> • ±1 minute/month at 25 °C • Extended Operation: ±20 minutes/month at 140 °C (±450 ppm) 	
Computer Interface	IFC400 or IFC406 USB docking station required; 125,000 baud	
Operating System Compatibility	Windows XP SP3 or later	
MadgeTech Software Compatibility	<ul style="list-style-type: none"> • MadgeTech Standard Software version 4.2.3.0 • MadgeTech Secure Software version 4.2.2.0 or later 	
Operating Environment	-40 °C to +140 °C (-40 °F to +284 °F), 0 %RH to 100 %RH, 0.002 PSIA to 100 PSIA	
IP Rating	IP68	
Dimensions (<i>body</i>)	1.89 in x 0.970 in x 0.970 in (48 mm x 24.6 mm x 24.6 mm)	
Dimensions (<i>probe</i>)	1.75 in x 0.0625 in dia. (0.188 in transitional dia.) 44.5 mm x 1.59 mm (4.78 mm Transitional dia.)	
Weight	65 g (2.3 oz)	
Materials	316 Stainless Steel	
Approvals	CE	

Disclaimer & Terms of Use

Listed specifications can be used to determine maximum allowable exposure times for the HiTemp140 with Thermal Shield at different temperatures beyond the normal operating range of the logger. Both the data logger and Thermal Shield must be at ambient temperature (*approximately 25 °C*) before being placed in the extreme temperature environment.

Immediately following exposure to high temperature, the data logger should be removed from the thermal shield (*using appropriate precautions, as it could be VERY hot*) OR the data logger and shield should be placed in a water bath (*approximately 25 °C*) for at least 15 minutes to allow it to cool. Failing to do this may allow heat trapped in the Thermal Shield to continue to heat the data logger to potentially unsafe levels.

If your application involves a ramp up to a temperature above 140 °C and/or any complex temperature profile that isn't simply a constant temperature, please contact MadgeTech to determine whether the HiTemp140 with Thermal Shield is suitable.

Please provide MadgeTech with a detailed description of your temperature profile, including temperatures, durations, ramp times, and process media (*air, steam, oil, water, etc.*) If MadgeTech is unable to definitively calculate the suitability of our product for your application, we can provide a test unit outfitted with a high temperature indicator sticker. This sticker has an indicator dot which will turn black if exposed to temperatures above 143 °C. Apply the sticker to the bottom of the data logger itself (*not the thermal shield*), remove the battery for safety, place the data logger into the thermal shield and run the assembly through the proposed temperature program. The first indicator dot on the sticker will turn black at 143 °C. If that happens, the HiTemp140 with thermal shield is not appropriate for the application and we will work to find a solution that is.

MadgeTech, Inc.

6 Warner Road • Warner, NH 03278

Phone (603) 456.2011 • Fax (603) 456.2012

madgetech.com • info@madgetech.com